

DX1002-T

The DX modular housing arrangement offers a flexible and space conscious solution to integrate our innovative DXO Cartridge in to both new and existing systems. The Delta-Xero system can be configured up to 12 cartridges in parallel as a single unit in a compact and easily maintainable layout.

The unit can be supplied with a number of standard options to provide an effective fluid conditioning and monitoring package to suit the majority of systems. The flexibility of the unit allows tailoring to customer's specific requirements.





V -		_	
жи	T O T	02	_

Drive Input	Electric or Pneumatic		
Connection Ports	3/8"BSP In & Out		
Flow Indicator	Visual		
Suggested System Volume	Up to 9000l @ 32cSt		
Particulate Removal	From 0,1 µ		
Weight	25 kg		
Dimensions	H g16 mm x D 300 mm x L 550 mm		
Material	SS316		
DXO Cartridge QTY	2		


Flow Rate varies depending on viscosity, pressure and temperature


Approx	32 cSt	46 cSt	68 cSt	100 cSt	220 cSt	320 cSt	460 cSt
flow at 2.7	2.5 l/min	2.0 l/min	1.6 l/min	1.2 l/min	0.8 l/min	0.4 l/min	0.2 l/min
bar:							
Oil Volume	9000ltrs	7000ltrs	6000ltrs	4800ltrs	3600ltrs	1600ltrs	800ltrs





DX1002-T

General Arrangement









DXO Cartridge

Contamination capacity:	Up to 4.5kg per DXO		
Water absorption, free and bound:	2600ml		
Material insert:	PP Cellulose mix		



